


New tools for TLC/HPTLC

The new *smartACCESSORIES* line from CAMAG makes chromatographer's life easier.

smartCUT

to cut TLC/HPTLC plates easily and most precisely.

- Cuts plates with a thickness up to 3 mm
- Does not damage the sensitive layer
- Easy to handle. Read the required size from the scale directly
- Helps saving costs on precoated plates of high quality by preventing offcuts.



smartALERT

to do TLC/HPTLC plate development "always right".

- Guarantees that the developing distance will always be accurate and according to the method
- Gives acoustic and visual notice when the mobile phase has reached the desired developing distance
- Replaces the unreliable timer or the stop watch
- Works with glass tanks for plate sizes 20 x 20 cm, 20 x 10 cm and 10 x 10 cm
- No wastes because of "over-developed" plates.



www.camag.com/smartaccessories